



EQUIPMENT
SELECTION
MADE EASY




MORTUARY CATALOGUE

1300 133 120 | sales@aidacare.com.au | aidacare.com.au

Funeral & Mortuary

4

Funeral Home & Mortuary Equipment



Funeral Home & Mortuary Equipment



Funeral Home & Mortuary Equipment

Aidacare Aspire A320 Aluminium Bariatric Lifter



Ergonomic Handles & Support Arms
Offer multiple grip points, assistance with Gait Training and leverage for turning



Ergonomic Handset
Linak technology fits neatly in the hand with an intuitive control panel



Powered Leg Function
Opens and closes the legs for lifting stability or accessibility



Quick Release 4 Point Sling Bar
One touch release and attach mechanism



Safety Features
Emergency stop button, emergency lowering and anti-entrapment technology



TENTE Castors
2 x 100mm front castors
2 x 125mm rear locking castors



1 YEAR WARRANTY Battery

3 YEAR WARRANTY Electronics

5 YEAR WARRANTY Frame



Sova Chapel Trolley

Compact 1170 x 500mm platform

Durable PVC top surface

Removable battery pack

Linak electrics 24 volt system

200mm diameter rubber tyres for smooth transfer

- Easily transfer coffin without having to manually lift
- High/low operation accommodates any vehicle height
- Electric high/low operation. Optional skirt allows trolley to transform to a chapel stand. Electric casket brake.
- Electric casket lock front and rear
- Zinc epoxy coated frame
- Electric floor brake
- 200mm diameter rubber tyres for smooth transfer
- Linak electrics 24 volt system



sova / dignity in motion

Bearing rollers

Up to 350kg load capacity

Electric casket lock front and rear

Electric floor brake

Zinc epoxy coated frame

High/Low adjustable
500 – 900mm operated via handset



Chapel Trolley – Fabric Skirt



Height Range 500 – 900mm

5 YEAR WARRANTY

Code	Description	Length	Width	Height	SWL
FUN100600	Chapel Trolley – with Skirt	1200mm	505mm	500 – 900mm	250kg
FUN100620	Fabric Skirt – Pair for Chapel Trolley				
FUN100610	Chapel Trolley – Extra Wide – with Skirt	1200mm	655mm	500 – 900mm	350kg
FUN100630	Fabric Skirt – Pair for Extra Wide Chapel Trolley				



Viking XL Patient Lifter



Informative control box displays number of lift cycles, battery level, lift overload and service indicator

Optional quick-release hook system which means caregivers can easily and rapidly change a slingbar or install a scale

Optional armrests help support patients during ambulation as well as making it easier for caregivers to manoeuvre the lift



Universal TwinBar 670 Slingbar offers additional sling space for patients of size

Intuitive and ergonomically-designed hand control incorporates indicators for low battery level and when the safe working load of the lift is exceeded

An extensive assortment of accessories is available including slings, slingbars and scales



2 YEAR WARRANTY Electronics

10 YEAR WARRANTY Frame



Code	Description	Overall Height	Overall Length	Overall Width	Lifting Height	Material	SWL
LSS393170	Viking XL Patient Lifter	2110mm	1420mm	815 – 1130mm	540 – 1910mm	Aluminium	300kg

CIRRUS⁵⁰⁰ Sova Ceiling Track Hoist

- Ceiling track system
- 270° rotation
- Adjustable length straps
- Heavy duty stainless steel hardware
- Ergonomic finger tip control pendent



sova / dignity in motion

- Inline cable management system
- 2 speed electric high/low operation
- Parallel strap lifting mechanism
- Head strap support




Code	Description	Overall Height	Overall Length	Overall Width
LIC355300	Cirrus 500 Ceiling Track Bodylifter Hoist – 500kg	300mm	1200mm	470mm
LIC355305	Weigh Scale for Cirrus 500 – Factory Fitted			
LIC355310	Pivot Trolley for Cirrus 500 270 Degree			
LIC355315	Cable Management for Cirrus 500 – Priced per m			

Coffin/Body Tray Trolley – 500kg

sova / dignity in motion

- Dual purpose roller design for coffin & body trays
- 150mm locking castors
- Heavy duty ball bearing rollers
- Stainless steel top & bottom frame
- Electric over hydraulic high/low operation
- Electric coffin/tray brake
- Maintenance free battery pack
- Electric/Hydraulic drive unit
- Electric Retractable drive wheel
- Variable speed controller
- Suspension system for uneven surfaces and superior traction
- Battery level indicator



Code	Description	Length	Width	Height
FUN100120	Coffin/Body Tray Trolley – Drive Unit	2460mm	780mm	400 – 1900mm
FUN100130	Coffin/Body Tray Trolley – Drive Unit and Tray Drive Roller	2460mm	780mm	400 – 1900mm
FUN100140	Coffin/Body Tray Trolley – Drive Unit and Weigh scale	2460mm	780mm	400 – 1900mm
FUN100150	Coffin/Body Tray Trolley – Drive Unit, Tray Drive Roller and Weigh scale	2460mm	780mm	400 – 1900mm
FUN100160	Concealment Option			

Coffin/Body Tray Trolley – 300kg

sova / dignity in motion

- Dual purpose roller design for coffin & body trays
- Linak actuators
- Heavy duty engineered polymer rollers
- Ergonomic push/pull handle
- Electric high/low operation
- Electric coffin/tray brake
- Maintenance free battery pack
- 150mm locking castors



Code	Description	Length	Width	Height
FUN100210	Coffin/Body Tray Trolley	2055mm	640mm	470 – 1825mm
FUN100220	Coffin/Body Tray Trolley – Side Loading	2320mm	640mm	470 – 1825mm
FUN101050	Coffin/Body Tray Trolley – Tray Roller	2170mm	640mm	470 – 1825mm
FUN101060	Coffin/Body Tray Trolley – Electric Drive Unit	2320mm	640mm	470 – 1825mm
FUN101070	Coffin/Body Tray Trolley – Drive Unit – Side Loading	2340mm	640mm	470 – 1825mm
FUN101080	Coffin/Body Tray Trolley – Drive Unit and Electric Tray/ Coffin Roller	2435mm	640mm	470 – 1825mm

Coffin/Body Tray Trolley – Concealment – 500kg

sova / dignity in motion

- Tarpaulin cover
- Gas assisted folding side rails
- Stainless steel side rails



Code	Description	Length	Width	Height
FUN101000	Coffin/Body Tray Trolley – Drive Unit w/ Concealment	2460mm	750mm	475 – 1900mm
FUN101010	Coffin/Body Tray Trolley – Drive Unit and Tray Drive Roller w/ Concealment	2460mm	750mm	475 – 1900mm
FUN101020	Coffin/Body Tray Trolley – Drive Unit and Weigh Scale w/Concealment	2460mm	750mm	475 – 1900mm
FUN101030	Coffin/Body Tray Trolley – Drive Unit, Tray Drive Roller & Weigh Scale w/ Concealment	2460mm	750mm	475 – 1900mm

Coffin/Body Tray Trolley – Concealment – 350kg

sova / dignity in motion

- Dual purpose roller design for coffin & body trays
- Linak actuators
- Heavy duty engineered polymer rollers
- Ergonomic push/pull handle
- Electric high/low operation
- Electric coffin/tray brake
- Maintenance free battery pack
- 150mm locking castors



Code	Description	Length	Width	Height
FUN101120	Coffin/Body Tray Trolley – Concealment – Drive Unit	2320mm	780mm	470 – 1825mm
FUN101130	Coffin/Body Tray Trolley – Concealment – Drive Unit – Side Loading	2320mm	780mm	470 – 1825mm
FUN101140	Coffin/Body Tray Trolley – Concealment – Drive Unit – Tray Roller	2435mm	780mm	470 – 1825mm

Embalming Trolley – 200kg

sova / dignity in motion

- Dual actuators
- 304 stainless steel top section
- Electric tilt function for easy draining
- Drain hole with hose
- Push handles both ends
- Corner buffers
- Electric tilt function for easy drainage
- 4 x buffers on corners



Code	Description	Length	Width	Height
FUN100300	Embalming Trolley – Fixed tray	2200mm	750mm	615 – 1015mm



Cadaver Tray - 350kg

- Stainless steel construction
- Push/pull handles both ends
- Angled sides allow for easy side transfer
- Tubular sub-frame
- Angled corners allow for easy cleaning and fluid removal

sova / dignity in motion



Code	Description	Length	Width	Height
4H810P	Cadaver Tray	2000mm	660mm	85mm
4H810PD	Cadaver Tray w/ drain	2000mm	660mm	85mm



Cadaver Tray - Bariatric - 500kg

- Stainless steel construction
- Push/pull handles both ends
- Angled sides allow for easy side transfer
- Sub-frame construction
- Angled corners allow for easy cleaning and fluid removal

sova / dignity in motion



Code	Description	Length	Width	Height
4H811P	Cadaver Tray - Bariatric	2000mm	750mm	85mm
4H811PD	Cadaver Tray - Bariatric with drain	2000mm	750mm	85mm



Single Bay Rack - 3 & 4 tier

- Open designs allows access for cleaning
- Rigid flat pack construction
- Stainless steel construction
- Adjustable stainless steel feet
- Optimised tier height
- Custom size can be designed
- 250 - 350kg SWL per bay
- Front and rear retainers

sova / dignity in motion

Code	Description	Length	Width	Height	SWL
FUN100520	Single Bay Rack - 3 tiers	2110mm	740mm	1690mm	250kg
FUN100530	Single Bay Rack - 3 tiers - Side loading	740mm	2180mm	1690mm	250kg
FUN100560	Single Bay Rack - 4 tiers - Cadaver Tray Storage only	2110mm	740mm	1900mm	350kg



Single Bay Rack - 3 & 4 tier - Mobile

- Open designs allows access for cleaning
- Rigid flat pack construction
- Stainless steel construction
- 100mm total lock castors
- Optimised tier height
- Custom size can be designed
- 350 - 500kg SWL per bay

sova / dignity in motion

Code	Description	Length	Width	Height	SWL
FUN100850	Single Bay Rack - 3 tiers	2110mm	740mm	1130mm	350kg
FUN100870	Single Bay Rack - Bariatric - 3 tiers	2110mm	955mm	1250mm	500kg
FUN100900	Single Bay Rack - 4 tiers				350kg
FUN100920	Single Bay Rack - Bariatric - 4 tiers				500kg



Sova Lifting Straps

- To be used in conjunction with the Morgue Sling (4 bands) to allow optimal transfers in morgue applications
- Suitable for use with Fixed Ceiling Lifts
- Compatible with Cirrus 500, Liko Ceiling Hoists, Liko Patient Lifters, Prism Ceiling Hoists, Aidacare A320, A205 and 200 Patient Lifters

sova / dignity in motion

Code	Description	Length	Width
LIC362400	Lifting Strap - Short - 2 eyelets - HDPE Plastic	1250mm	50mm
LIC362410	Lifting Strap - Long - 2 eyelets - HDPE Plastic	1475mm	50mm

Lifter Spreader Bar - 200kg

- Optional Stretch Leveller allows for quick adjustment
- Can be used with a full lift sheet or with 4 lift straps
- Lightweight design weighing at 7.2kg
- Optional quick-release hook system is also available
- Compatible with Liko patient lifters & Liko ceiling hoists, Prism ceiling hoists, Aidacare A320, A205 and 200 lifters



Code	Description	Length	Width	Height
LSS394920	Mortuary Spreader Bar - 200kg	1263mm	617mm	227mm

Sova Lifter Spreader Bar - 363kg

- Multiple hook positions - 13 total
- Simple and fast attachment
- Epoxy powder coat finish
- Central hanging pivot point
- Mild steel heavy wall tubular frame
- Suitable for use with ceiling mounted lift systems and floor hoists



Code	Description	Length	Height
LIC362300	Mortuary Spreader Bar - 363kg	1580mm	165mm

Ceiling Hoist - Motor - CP200 Portable

PRISM MEDICAL UK

- Slimline, low profile, padded carry bar that has six loop attachments as standard (four-point hook optional). Different width carry bars also available.
- Low profile hoist unit is unobtrusive and provides greater lifting height
- All lifting and traversing operations have soft start/stop to ensure smooth transfers for the patient
- Quick release sling bar



Code	Description	Suits
LIC350105	CP200 Portable Ceiling Hoist	Ceiling Hoist Gantry - LIC352120

Ceiling Hoist - Bariatric C380 Power Traverse

PRISM MEDICAL UK

- Carry bar fitted with Quick Release System for simple interchange of carry bars
- Emergency stop/emergency lower
- Smooth stop start
- Bariatric four point carry bar
- Low profile hoist unit provides a great lift height



Code	Description	Suits
LIC350260	C -380P Power Traverse (Carry Bar Separate)	Installed Ceiling Hoist Track - LIC353120K

Ceiling Hoist - Prism - Transactive Xtra Fixed



- The Transactive XTRA fixed ceiling hoist allows for a large array of configurations, catering to changing needs, making it a suitable fixed lifting solution
- Digital display screen provides essential information for the user and caregiver
- Return to Charge (RTC) option automatically returns the hoist to its charger when required
- Manual windup and raising allows the hoist to continue to be used during a power outage
- Low profile hoist unit is unobtrusive and provides greater lifting height
- Pneumatic handset is ideal for use in wet environments
- Smooth lifting/running tape with large lifting range
- Emergency Lowering allows for the safe lowering of the in emergency situations
- Client safety is assured with locking latches to secure slings in place for all lifts
- Slimline and with great lifting capacity
- Low profile hoist unit is unobtrusive and provides greater lifting height
- All lifting and traversing operations have soft start/stop to ensure smooth transfers for the patient
- A host of safety features
- Smooth running tape with large lifting range
- State of the art display with lift counter
- Available in manual or powered traverse options

Code	Description	Suits	Height	SWL
LIC350170	Ceiling Hoist - Transactive - Manual Traverse & Carry bar	Installed Ceiling Hoist Track - LIC353120K (ALL)	Up to 2080mm	200kg
LIC350180	Ceiling Hoist - Transactive - Powered Traverse & Carry bar			200kg
LIC350210	Ceiling Hoist - Transactive - Power Traverse & Carry bar			270kg
LIC350182	Ceiling Hoist - Prism - TXE200D (C450) - Powered - Return to Charge - 200kg			200kg



FreeSpan Gantry

- FreeSpan™ SR (straight -rail) is a flexible alternative for most overhead -lift situations.
- The lift system is freestanding, and since it is not affixed to the walls or the ceiling, there are no special strength requirements for those structures.
- FreeSpan™ SR is made of aluminium and many different rail lengths are available.
- Choose between using Multirall™ or LikoRall™ lift units.
- FreeSpan™ SR is assembled without tools and is equipped with wheels, which facilitate positioning.
- The wheels also make the lift system easy to move between different rooms.
- FreeSpan™ is also available in a traverse -model: FreeSpan™ Traverse, a unique, freestanding system that enables lifting and transfer of patients between many different lifting points.



3M Kit Includes:

- FreeSpan Side Support - Wheels + Charger plate parking bracket for sling bar
- FreeSpan Rail 3m - with LikoRall Trolley - 250kg
- Ceiling Hoist - LikoRall 250 ES - White 250kg SWL
- Spreader Bar - Liko Universal SlingBar 450 with Quick-release Hook - max 300kg
- Hand Control - LikoRall S, ES, 2 button (for lifting)
- Battery Charger - LikoRall and Multirall (24v/0,6 A)

5M Kit Includes:

- FreeSpan Side Support - Wheels + Charger plate parking bracket for sling bar
- FreeSpan Rail 5m - with LikoRall Trolley - 200kg
- Ceiling Hoist - LikoRall 242 S R2R - White 200kg SWL
- Spreader Bar - Liko Universal SlingBar 450 with Quick-release Hook - max 300kg
- Hand Control - LikoRall S, ES, 2 button (for lifting)
- Battery Charger - LikoRall and Multirall (24v/0,6 A)

Code	Description	SWL
LIC360730	FreeSpan Lift System - 3M Kit	400 -500kg
LIC360740	FreeSpan Lift System - 5M Kit	400 -500kg



Clax Cart Trolley

- Ideal for transporting small to medium size materials
- 2 tier folding trolley
- Lightweight and fully portable
- Foot brake and removable wheels
- Extra boxes available
- 46 litre capacity
- Safe working load upper tray 20kg, lower tray 40kg
- Folded Dimensions 670 x 470 x 110mm

Code	Description	Length	Width	Height
WAT758020	Folding Trolley - Clax w/ crate	890mm	550mm	1030mm
WAT758021	Crate for Clax trolley	890mm	550mm	1030mm



Grave Spreader

- Epoxy powder coated
- Adjustable width settings

Code	Description
FUN100730	Casket Lowering System - Manual


Casket Lowering System

Strap lowering aid

Lever action swing away casket rollers

Epoxy powder coated steel frame

Lightweight aluminium surround



End stopper/guide

Safety rail

Heavy duty construction

Grave surround to prevent cave-ins


Fabric skirt - optional




Casket Lowering Device



Storage & Transport Trailer



Grave Surround



Grave Surround Covers



Skirt

Code	Description	SWL
FUN100700	Casket Lowering System - Manual	350kg
FUN100710	Casket Lowering System - Electric	350kg
FUN100720	Aluminium grave surround to suit casket lowering system	1000kg
Available upon request	Grave Surround Covers - Set	350kg
Available upon request	Storage and Transport Trailer	
Available upon request	Skirt	

